



Stopwatch, Water Resistant

Product #:	2630200
ZAR Price:	Contact Hach
Ships within 1 week	

Counts up to 24 hours with resolution of 1/100 second for first 30 minutes, 1 second thereafter. Features lap function, alarm clock, and calendar. Button cell battery included. Dimensions: 5.4 x 6 cm. (2.4 oz). NIST-certified.

Stopwatch Mode

Recalls split and lap times as well as the slowest, fastest & average laps.

Timer Mode

With 3 modes: count down and stop, count down and repeat, count down and then count up.

Clock Mode

Selectable for 12 or 24 hour format, with alarm clock, calendar and hourly chime modes.

Stroke Mode

Calculates average strokes, beats or pulses per minute based on the timing of 3 sample strokes.

Pacer Mode

Set from 5 - 240 beeps per minute.

Specifications

Accuracy 2:	0.01 sec
Length:	54 mm
Quantity:	1 each
What's included?:	Includes: Stopwatch and lanyard

What's included?

Includes: Stopwatch and lanyard