



Orbisphere Hydrogen (H₂) TC Sensor with carbon dioxide purge, protection cap, ext. temp. sensor (20 bar)

Product #: 31292TC
ZAR Price: Contact Hach

Allows you to monitor hydrogen in the power production process.

Standard Hydrogen TC sensor with carbon dioxide purge and protection cap. With with external temperature sensor adapter.

Sensor cable to be ordered: 32505.03.

Maximum pressure: 20 bar

This sensor is the successor model for 31252H and 31252GP.

Unique thermal conductivity (TC) sensor design

Selective and precise measurement of hydrogen in gaseous or liquid samples

No specific sample preparation required, the gas concentration is measured directly in the sample

Rugged construction can handle harsh plant conditions and high sample pressures

Flexibility of installation for better process control and very low maintenance

Specifications

Accuracy:	(Sample temp. 20 - 50°C within ± 5°C of calibration temperature)
	The greater of
	Membrane 29561A: ±1% of reading, or ±2 ppb, or ±0.03 cc/kg, or ±1.5 bar
	Membrane 2952A: ±1% of reading, or ±8 ppb, or ±0.1 cc/kg, or ±6 mbar
	Membrane 2935A: ±1% of reading, or ±25 ppb, or ±0.4 cc/kg, or ±20 mbar
Application:	Power
Purge connection:	Carbon Dioxide Purge
Range:	Range at 25 °C
	Membrane 29561A: 0 - 2 ppm, or 0 - 25 cc/kg, or 0 - 1.5 bar
	Membrane 2952A: 0 - 10 ppm, or 0 - 120 cc/kg, or 0 - 6 bar
	Membrane 2935A: 0 - 20 ppm, or 0 - 220 cc/kg, or 0 - 12 bar
Sample Pressure:	0 - 20 bar
Temperature Range:	-5 - 50 °C

Weight:	0.95 kg
What's included?:	Sensor only.
	Controller, sensor cable, flow-chamber or process connection must be ordered separately.

What's included?

Sensor only.Controller, sensor cable, flow-chamber or process connection must be ordered separately.